



东莞中力仪器科技有限公司

ZhongLi Instrument Technology Co., Ltd.

Introduction

Name: ZL-1034A Vacuum Impregnation Machine (Single Cylinder)



Tel: [+86-769-8928 0588](tel:+86-769-89280588)

Fax: [+86-769-8928 0988](tel:+86-769-89280988)

Website: www.zltester.com

E-mail: Zhongli@zltester.com

Address: [No.62, Xinhe Management of Area, Wanjiang District, Dongguan city, Guangdong province ,China](#)



Main Features:

1. This machine adopts man-machine interface (Weilun color 7 inch) touch screen + (Mitsubishi) PLC control; All parameters can be programmed through the man-machine interface, and can store 0-50 different data sets.
2. By the stepper motor control the level of rise and fall, the height of the liquid level adjustable (0.1-60mm) and speed adjustable.
3. And the dipping time adjustable (0-999 seconds), at the same time with the alarm time, the second vacuum, automatically into the air, automatically open the lid and other functions.
4. The vacuum pump selection XD-020-380V, vacuum rapid, vacuum can be set (time control)
5. The vacuum box L700 * W 530 * H400 selection of high quality steel GB 6mm, vacuum cover selection of international quality steel welded together.
6. Sealing system used 12mm imported silicone seal for sealing.

Automatically open the lid, automatic charge and discharge gas, liquid level automatic lift, PLC + touch screen control, can effectively prevent the pin dip paint, reduce the secondary solder!

